





The X-Y system features a movable 3rd track that permits precise positioning of the lifted person anywhere under the X-Y systems range.

Selection is based on distance between fasteners and the ceiling lift capacity.

The distance between fasteners is the maximum permitted between fasteners wall posts or parallel tracks of the X-Y.

Ceiling fastened track



X-Y System

KWIKtrak

TRACK SIZE

| MAXIMUM DISTANCE BETWEEN FASTENERS FOR FIXED TRACK SECTIONS | | | | | |
|---|------|-------|--------|---------|---------|
| CEILING LIFT CAPACITY | | | 90 MM | 140 MM | 180 MM |
| KG | LB | ST | | | |
| 200 | 440 | 28.57 | 2.50 m | 4.50 m* | 6.00 m* |
| 270 | 600 | 42.86 | 2.15 m | 4.15 m | 5.80 m |
| 360 | 800 | 57.14 | 1.85 m | 3.60 m | 5.00 m |
| 455 | 1000 | 71.43 | 1.65 m | 3.20 m | 4.50 m |

*Maximum length available

| CEILING LIFT CAPACITY | | | MAXIMUM UNSUPPORTED SPAN OF THE MOVING 3 rd TRACK ON AN X-Y SYSTEM DISTANCE IS EXPRESSED IN METERS | | | | | | | | | | | | | | | | | |
|-----------------------|------|-------|--|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|
| KG | LB | ST | 1.75 | 2.00 | 2.25 | 2.50 | 2.75 | 3.00 | 3.25 | 3.50 | 3.75 | 4.00 | 4.25 | 4.50 | 4.75 | 5.00 | 5.25 | 5.50 | 5.75 | 6.00 |
| 200 | 440 | 28.57 | HO | HO | HO | HO | HM | HM | HM | HM | HM | HM | HM | HM | HM | HL | HL | HL | HL | HL |
| 270 | 600 | 42.86 | HO | HO | HM | HM | HM | HM | HM | HM | HM | HM | HL | HL | HL | HL | HL | HL | NR | NR |
| 360 | 800 | 57.14 | HO | HM | HM | HM | HM | HM | HM | HM | HL | HL | HL | HL | HL | HL | NR | NR | NR | NR |
| 455 | 1000 | 71.43 | HM | HM | HM | HM | HM | HM | HM | HL | HL | HL | HL | HL | NR | NR | NR | NR | NR | NR |

HO - KWIKtrak 90mm - Standard span

HM - KWIKtrak 140mm - Medium span

HL - KWIKtrak 180mm - Long span

NR - Not recommended

ACCESSORIES

| | | |
|---|------------|---|
| A | #700.11295 | XY Flush mount trolley KWIKtrak |
| B | #700.12300 | XY Trolley Kit 455 kg KWIKtrak |
| C | #700.15570 | XY retaining assembly KWIKtrak |
| D | #700.15510 | XY Charger Interface KWIKtrak (To use with #700.11290) |
| E | #700.11285 | XY Short trolley |

